

AT-216 Personal FM System

216 MHz

Creates A Direct Link Between Listener and Speaker • Hearing Aid & Cochlear Processor Compatible

At work, home, or on-the-go, the AT-216 gives you a close-up on sound. With internal audio processing that emphasizes the frequencies that define speech intelligibility, the AT-216 produces the highest fidelity available from any personal FM system. Incorporating unique options and accessories, it affords users the ability to effectively communicate in difficult listening environments. Not only are FM systems the best way to improve signal-to-noise ratios to overcome the listening challenges of distance, background noise, and reverberations, FM systems also significantly improve the effectiveness of hearing aids and cochlear processors. The NTC-102 neckloop provides a wireless connection to hearing aids and ear-level cochlear processors equipped with a telecoil (T-switch).

A unique environmental microphone feature adds even more functionality to the AT-216. It provides the listener with the ability to hear sounds from two sources: from the M-216 transmitter and from the PR-216 receiver's environmental microphone. The receiver's environmental microphone comes in one of two options:

Enviro-Mic: Combines environmental sounds from the receiver's microphone with audio from the transmitter so that both sound sources are heard together.

Smart-Mic: Prioritizes the transmitter's audio over environmental sounds from the receiver's microphone. When no sound from the transmitter is present, the environmental microphone on the PR-216 receiver automatically activates. When sound from the transmitter is present, the receiver's environmental microphone automatically mutes to help block out background noise.



The micro-mini jack on the PR-216 receiver uses the M-4020P plug-in environmental microphone for either the Enviro-Mic or Smart-Mic option. This input jack may also be used with other accessories such as handheld directional microphones, clip-on speech training microphones, and telephone adapters.



Complete AT-216 System Includes:

- 1 x M-216 Personal Transmitter
- 1 x CM-183 RT Omnidirectional Lapel Microphone
- 1 x TM-10 Conference Table Microphone Adapter
- 1 x PR-216 Receiver with Enviro-Mic or Smart-Mic Option
- 1 x M-4020P Plug-in Environmental Microphone
- 1 x NTC-102 Neckloop Transducer
- 1 x SM-N Earphone Assembly or LS-3 Headphone
- 1 x NBC 9-3-2 Battery Charger
- 2 x NH9-200 Ni-MH Rechargeable Batteries
- 1 x CB-36 ST Aux Audio Input Cable
- 2 x BC-216 Snap-on Belt Clip
- 1 x C-216 Carrying Case

COMTEK®
First Quality In Wireless Sound

P: 800-496-3463

www.comtek.com