

Hocker Incorporated

www.hockerinc.com

13402 Weiman Road Houston, TX 77041 713-464-5829 Fax 713-464-3192

Performance Evaluation
UV & White Light Meter

 Customer PO #:
 86600

 Certification #:
 24-0269

 Evaluation Date:
 Due Date:

 2/26/2024
 8/26/2024

 DLM-1000
 Equipment Condition

Yes F-LTMT-1 Operational When Received? **Equipment Condition** When Received? Company: P & B Testing, Inc. In Tolerance when Yes Received? Address: 6645 W. Tidwell New City: Houston Good Equipment Description: **Dual Light Meter** State: TX Fair Model:DLM-1000 Poor Zip: 77092 Phone: N/A S/N:121241A,B,C Email: qa@pbtesting.com Failed Country: USA

Contact: Buck Snider File Loc. P & B Testing, Inc._45348_24-0269

Serial #: NIST#: Equipment Used For This Eval.: Cal. Date: **Due Date:** 23111/01/24 01660 8/7/2024 2/7/2024 Gould Bass DLM-1000 A Readout 071074 A 23111/01/24_01660 2/7/2024 8/7/2024 071074B.C Gould Bass DLM-1000 B UV & WL Sensors 5/4/2024 5/4/2023 1821-1039/1106078/9000-1315/01607 #040014000 LASCAR EL-GFX-2 Temp/HUM Logger **Equipment Mfg.:**

Tolerance %: Digital 3 pcs. Gould Bass

Equipment Owner:Address:City:State:Zip:P & B Testing, Inc.6645 W. TidwellHoustonTX77092

DLM-1000 "B" Sensor					Temperature:		71°F	Humid.:	44%
UV As Found	No. 2 872	UV Meter A	s Received		UV As Left	UV Meter No Adjustment or Repair Required			
uW/sq.cm	uW/sq.cm	uW/sq.cm	% Diff.	Tolerance	uW/sq.cm	uW/sq.cm	uW/sq.cm	% Diff.	Tolerance
Ideal	Actual	Difference		400 mm mm m	Ideal	Actual	Difference	Company To Local	acalterian p
0	0	0		ln	0	0	0		In
740	730	-10	-1.4%	In	740	730	-10	-1.4%	ln .
2780	2690	-90	-3.2%	In	2780	2690	-90	-3.2%	ln
4880	4750	-130	-2.7%	In	4880	4750	-130	-2.7%	ln
Maximum Deviation -130 -3.2%			Maximum	Deviation	-130	-3.2%			

DLM-1000 "C" Sensor


Ban see e conce:										
WL As Found	White Light Meter As Received				WL As Left	White Light MeterNo Adjustment or Repair Required				
Foot Candles	Foot Candles	Foot Candles	% Diff.	Tolerance	Foot Candles	Foot Candles	Foot Candles	% Diff.	Tolerance	
Ideal	Actual	Difference			Ideal	Actual	Difference			
0.0	0.0	0.0		ln -	0.0	0.0	0.0		In	
4.0	4.0	0.0	0.0%	In	4.0 .	4.0	0.0	0.0%	In	
106.0	106.0	0.0	0.0%	In	106.0	106.0	0.0	0.0%	ln	
653.0	648.0	-5.0	-0.8%	In	653.0	648.0	-5.0	-0.8%	ln	
Maximum Deviation		-5	-0.8%		Maximu	m Deviation	- 5	-0.8%		

Fair Condition AS Received - both sensor lenses had testing material covering them AS FOUND / AS LEFT <5% @ each test point for both UV & visible Light sensors - Adjustment not required for calibration


Certification # Evaluation Date

24-0269 2/26/2024


P & B Testing, Inc.




UV Sensor AS Left



White Light Sensor AS Found



White Light Sensor AS Left



Hocker Incorporated calibration procedure CP-LTMT- 1 Was utilized for this perfomance evaluation /report of findings. CP-LTMT-1 accords and complies with to ANSI/NCSL-Z540, ASTM E-1444/*, ASTM E-709, ASTM E-1417 (where applicable) Master Transfer standards and metrology equipment used to perform this evaluation are traceable to the National Institute of Standards and Technology (NIST) through SI. Referenced numbers listed in this document are on file with supporting documentation.

In Conformance with 10CFR21. ANSI/NCSL 2540.3-2006 & ISO10012.

Technician Signature:

F-LTMT-1 5/24/2022 CP-LTMT-1 05 24 2022

Technician Performing Evaluation:

Derrick/Schumann

Date 2/26/2024

Approval Signature:

Approved By:

Lewis Brittain

An ISO 9001:2015 Registered Company

Buck Snider