

COMPOSITES | GLASS IONOMERS | TOOTH WHITENING | SDF RIVA STAR | EQUIPMENT CEMENTS | ADHESIVES | ETCHANTS SEALANTS | AMALGAMS | ACCESSORIES



SDI (North America) Inc. www.sdi.com.au/en-us Toll Free: 1-800-228-5166

WHITENING

IN-CHAIR WHITENING STARTUP PROMOTION! PURCHASE THE RADII XPERT



TAKE-HOME WHITENING

POLA DAY, POLA NIGHT & POLA LIGHT

POLA DAY

HYDROGEN PEROXIDE BASED ADVANCED TRAY TOOTH WHITENING SYSTEM

- Available in **7.5%** and **9.5% hydrogen peroxide** applications
- High water content
- From 30 minutes once a day

POLA NIGHT

CARBAMIDE PEROXIDE BASED ADVANCED TRAY TOOTH WHITENING SYSTEM

- Available in 10%, 16% and 22% carbamide peroxide
- From 45 minutes once a day
- Contains fluoride





Pola Day and Pola Night 4 and 10 Syringe Refills

COMPLETE YOUR WHITENING OFFERING WITH POLA LIGHT

- No custom trays required
- Reduced patient consult time
- Entry level whitening option
- Great front desk conversation starter

A PROFESSIONAL SOLUTION FOR ALL YOUR PATIENT NEEDS

POLA LIGHT 9.5%

- 1 x Pola LED mouthpiece
- 4 x 3g Pola Day 9.5%
- tooth whitening syringes 1 x USB charging cord
- POLA LIGHT 22% 1 x Pola LED mouthpiece 4 x 3g Pola Night 22%
- tooth whitening syringes 1 x USB charging cord

DISPENSER KITS

Pola Day and Pola Night 50 x 3g Syringe Refills









Pola Light Refill

SYRINGES



GLASS IONOMERS

BULK FILL GLASS HYBRID RESTORATIVE SYSTEM

When dentin is missing, use Riva Self Cure to replace it. It is the best dental material available today that virtually mimics dentin. No adhesive is required, and sensitivity is non-existent.

- Contains SDI's proprietary ionglass™, a high ion releasing, radiopaque, bioactive glass that remineralizes and prevents secondary caries formation
- Very high fluoride releasing and recharging ability
- Choice of viscosity High Viscosity formulation is flowable enough to inject
 and highly sculptable and packable
- Exceptional Handling; Non-sticky, non-slumping and sculptable formulation

BUY ANY 2 BOXES

GET A BONUS PREMIUM APPLICATOR 2

- Easy Activation Capsule 70% easier to activate
- · Ideal materials for dentin replacement
- · Radiopaque

RIVA

RIV

• BPA & HEMA free



THE MULTI AWARDED EASY HANDLING GLASS IONOMER

[50 CAPS]

Riva Light Cure has excellent resistance to common stains such as black tea and red wine.

- Contains SDI's proprietary ionglass™, a high ion releasing, radiopaque, bioactive glass that remineralizes and fights against secondary caries formation
- Exceptional handling; easy to sculpt and non-sticky available in both regular and high viscosity
- Unique, patented, orange light safe tip, prevents curing in the tip and significantly extends working time
- Easy Activation Capsule 70% easier to activate
- Highest color stability to tea & coffee
- Excellent marginal integrity
- Long term wear resistance due to high surface hardness
- High flexural strengths
- BPA free





BIOMIMETIC FORMULA

COMPOSITES

LUNA 2 AND LUNA FLOW

LUNA 2

JFW

Luna 2 is the next generation Luna universal composite. Luna 2 has an improved unique blend of fillers that were researched and developed at SDI to deliver the enhanced handling, very high radiopacity and reliable mechanical properties. Luna 2 is BPA free for healthconscious patients. Luna 2 makes placing a composite easier than ever.



Images courtesy of Dr. Susan McMahon - USA





HIGH FLEXURAL STRENGTH 130MPa

പ

HIGH POLISH AND WEAR RESISTANCE

Scan QR code for more information

JANUARY ONLY! BUY 2 GET 1 FREE FEBRUARY & MARCH 3+1 OR 20+10



LUNA FLOW

Luna Flow is a new extra strong flowable composite that is available in two viscosities. With a blend of fillers in different ultrafine sizes to optimize handling, mechanical and optical properties, Luna Flow offers high radiopacity, control over the application, easy and accurate shade matching with color stability, excellent strength and wear resistance.



Such properties make Luna Flow a fantastic universal option for liner; base; provisional or restoration repairing; and Class V; amongst other indications.



Images courtesy of Dr Jose Amengual Lorenzo - Spain



HIGH POLISH FOR

EXCELLENT RESULTS



265% AI







Scan

QR code

for more information

HIGH FLEXURAL STRENGTH 128MPa



COMPOSITES

JANUARY ONLY! BUY 2 GET 1 FREE FEBRUARY & MARCH 3+1 OR 20+10





LUNA 2 UNIVERSAL COMPOSITE

- Improved non-stick, non-slump handling and reliable mechanical properties
- Logical Shade Matching Technology for easier and accurate shade selection
- BPA free
- Very high radiopacity of 250% AI



AURA

ULTRA AESTHETIC UNIVERSAL COMPOSITE

- 8 dentin shades and 3 enamel shades to reproduce the natural colors of teeth
- A simple layering technique with zero guesswork
- Superior strength and wear resistance
- High polishability and gloss
- Ultra High Density (UHD) filler with low-shrinkage resin
- High flexural strength



AURA EASY

UNIVERSAL COMPOSITE

- 4 shades cover 16 VITA® classical A1-D4® shades
- Increased wear resistance and strength
- Smooth high gloss finish every time
- Non-sticky consistency makes it simple to sculpt
- · Low volumetric shrinkage to offset marginal stress

AURA EASYFLOW

UNIVERSAL FLOWABLE COMPOSITE

- Higher radiopacity than enamel
- Does not slump
- Very high compressive strength 421 MPA!
- Flexural strength ideal for Class V
- Established nanohybrid filler system
- Optimal flow for cavity adaptation





AURA BULK FILL

UNIVERSAL BULK FILL COMPOSITE

- \cdot $\,$ One bulk fill placement up to 5mm depth of cure
- 20 sec. LED light cure
- · Natural-looking finish with just one universal shade
- Easy placement in a matter of seconds
- The waxy consistency is packable and non-sticky to optimize handling



ALLOYS

PURCHASE ANY RANGE OF SDI COMPOSITE REFILLS (LUNA, AURA RANGE) OR RIVA RANGE REFILLS (50 CAPSULE) AND RECEIVE **FREE ALLOY!**



Must be on one order to qualify for free goods.

BUY 2 GET 1 FREE



GS-80

ECONOMICAL, HIGH STRENGTH, ADMIX AMALGAM

- High early compressive strength
- Non-gamma 2 for great corrosion resistance
- Great corrosion resistance
- Excellent marginal sealing



PERMITE

HIGH STRENGTH, EASY CARVINGADMIX AMALGAM

- · Void-free restorations with no marginal leakage
- Superior handling characteristics
- High silver and non-gamma 2 for great corrosion resistance



LOJIC+

HIGH STRENGTH, HIGH SILVER SPHERICAL AMALGAM

- Creamy consistency, soft packing and smooth carving
- Very high compressive strength
- World's first platinum modified spherical amalgam

EQUIPMENT

RADIOMETER X

LED LIGHT CURING METER



OUTSTANDING ACCURACY. NO CALIBRATION. NO DELAY.

Compatible with all LED curing lights, the new Radiometer X accurately checks LED intensity to confirm your curing performance

- No calibration: Simply point and measure. No need to enter dimensions
- No dependence: No pairing, No apps, No display delay
- 5 year warranty.

STUDY: PROVEN ACCURACY

Results from a study of 7 radiometers and 23 curing lights has confirmed the outstanding accuracy of the Radiometer X.



Source: Dr Carlos Jose Soares (PhD)

 Radii Plus; Radii Cal; Radii Xpert/Monowave tip; Radii Xpert/Multiwave tip.
 Bluephase Meter II includes a LED diameter checker. Accuracy readings will vary if the user enters an incorrect diameter or includes the LED casing as part of the diameter.

BUY A RADII CAL CX GET A Bonus radiometer X





ADHESIVES

THE ALL-IN-ONE **ADHESIVE SOLUTION FOR EVERY SITUATION**

IMPROVED BOND STRENGTH AND DEFENDS AGAINST CLINICAL VARIABILITY

- Consistent bond strengths to dentin and enamel
- Wet and dry dentin bonding
- Proprietary combination of adhesive monomers including MDP
- Predictable bond strengths to indirect substrates
- Effective hybridization .
- Exceptional control .
- Highly aesthetic
- Pleasant aroma

BUY 1 GET 1 FREE*

*LIMITED TO 1 OFFER PER OFFICE

862 uses and zero post-op sensitivity

Dental Advisor Clinical Evaluation 2021.

MARIANNA OSIPOVA

NYC Metro and Northern NJ Cell: (718) 308-5588 Marianna.Osipova@sdi.com.au

MARK GUZIOR MA, ME, NH, CT, VT, RI Cell: (603) 553-3121 Mark.Guzior@sdi.com.au

CARRIE COOMER OH, KY, Southern IN Cell: [937] 214-7410 Carrie.Coomer@sdi.com.au

iern NJ

COMPOSITES | GLASS IONOMERS | TOOTH WHITENING | SDF RIVA STAR | EQUIPMENT | CEMENTS | ADHESIVES | ETCHANTS | SEALANTS | AMALGAMS | ACCESSORIES



EASTERN REGION

JUSTIN JOURDAN Eastern Regional Sales Manager Cell: (224) 240-1791 Justin.Jourdan@sdi.com.au

PHILLIP ZHOU PA, DE, Southern NJ, MD Cell (717) 395-0599 Phillip.Zhou@sdi.com.au

SHANTELLE BYRD

Michigan, Northern IN Cell (313) 520-4114 Shantelle.Byrd@sdi.com.au

facebook.com/sdinainc 🔘 instagram.com/sdinainc

YOUR **OUR** Smile. **Vision.**

SDI (North America) Inc. 1279 Hamilton Parkway Itasca, IL 60143

COLLEEN BURNS

Cell: (561) 358-9291 Colleen.Burns@sdi.com.au Colleen.burnoce. DINORAH ROBLES

Central/Northern IL, WI Cell: (630) 542-7988 Dinorah.Robles@sdi.com.au

JIM POTEAT GA, SC, NC, TN Cell: (704) 995-7303 Jim@Poteatdentalsolutions.com

Fax: 630-361-9222 usa.canada@sdi.com.au

MIKE MATUCH Upstate NY, Erie/Pittsburg, PA, WV Cell: (716) 913-8354 Michael.Matuch@yahoo.com

MIKE MATUCH

LOUIE KALOUDIS

Cell: (630) 363-9224 Louie:Kaloudis@sdi.com.au

Toll Free 1 800 228 5166 www.sdi.com.au

Redeem your free goods by sending your invoice to: usa.canada@sdi.com.au or fax 630-361-9222

Please allow 2-4 weeks for delivery. Please note offers cannot be combined. Offers cannot be used in conjunction with contract pricing. Valid on invoices dated January 1st - March 31st, 2023. All claims for free goods must be made within 60 days from the end of promotion date. **Purchases must be on one order to qualify for free goods**. Free products must be of equal or lesser value. Offers are valid in the US only.

WESTERN REGION

SDI

ZIPBOND UNIVERSAL ADHESIVE

MADE IN AUSTRALIA 5mL

DAN NIEHOFF Peninnal Sales & National Accounts

Regional Sales & National A Manager - Western Region Cell: (424) 212-3742 Dan.Niehoff@sdi.com.au

MARY ABOUSEIBAA Los Angeles, ventura, Kerri Couri Santa Barbara County Cell: [213] 330-9341 Mary.Abouseibaa@sdi.com.au

JASON KUPISCH No. Cal, Reno, NV, LA, AR, MS Cell: [224] 840-5127 Jason.Kupisch@sdi.com.au

JENNIFER BOLION OC, San Diego, Las Vegas, HI Cell: (949) 413-9035 Jennifer.Bolton@sdi.com.au LORI KELLAR WA, OR, AK, ID, MT Cell: (206) 696-1485 Lori.Kellar@sdi.com.au

JENNIFER BOLTON

KARLYN RASMUSSEN-DODD Cell: (832) 928-6938 Karlvn.Rasmussen-dodd@sdi.com.au CO, UT, WY, NM, El Paso, AZ Cell: [720] 635-3400 Zaffinoenterprise@gmail.com TIM VANWYCHEN MN, ND, IA, SD, NE Cell: (651) 231-2801 VanWychen@hotmail.com

KAREN ZAFFINO

DOUG SCHROEDER MU, KS Cell: (314) 422-0061 dsiltd@charter.net

FOR TECHNICAL QUESTIONS, PLEASE CALL OUR SDI PRODUCT EXPERTS AT 1-800-228-5166 AND PRESS 2



29 CLINICAL EVALUATORS 862 TOTAL USES

93% CLINICAL RATING

- Dental Advisor rates Zipbond ++++ 1/2 or 93% clinical rating
- 862 uses and zero post op sensitivity
- 97% of Dental Advisor evaluators rated it either equal or better than their existing adhesive
- 100% would recommend Zipbond to a colleague