



CIRIO GERMANO & C. snc

SPINNING HEAD to close polylaminate capsules (manual version)

****manual SPINNING HEAD 1400 rpm**

To close aluminium/polylaminate/tin foil capsules

Voltage 380 -50 hz.threephases or Voltage 220-50 hz.single phase


Version : On horizontal base for table

On vertical stand

On pneumatic vertical stand

Standard spinning head: max Ø capsules mm.31,5

Magnum spinning head: max Ø capsules mm.47






CIRIO GERMANO & C. snc

THERMAL HEAD to close pvc capsules (manual version)

THERMAL HEAD

To close pvc capsules with
diameter mm.42 and mm.55 max
Voltage 220-50 hz
Production 600 bottles per hour
Version: On vertical stand
On pneumatic vertical stand






CIRIO GERMANO & C. snc

EINBLOCK 1-4-6-8 HEADS **WITH DISTRIBUTOR CAPSULES**

(version with spinning head to close
polylamine/tin-foil capsules and
with thermal head to close pvc capsules)



CIRIO GERMANO & C. snc



EINBLOCK- automatic (1 HEAD)
DISTRIBUTION AND 1 HEAD CLOSING
CAPSULES


(SPINNING HEAD OR THERMAL HEAD
INTERCHANGEABLE)

PRODUCTION 1000 BOTTLES PER HOUR POLYLAMINATE CAPS
1800 BOTTLES PER HOUR PVC CAPS



EINBLOCK- automatic (4 HEADS)
DISTRIBUTION 1 HORIZONTAL LEVEL
AND 4 HEAD CLOSING CAPSULES

(SPINNING HEAD OR THERMAL HEAD)
PRODUCTION: MAX 3000 BOTTLES PER HOUR



EINBLOCK 4-6-8 HEADS
+DISTRIBUTOR CAPSULES C6 (2
LEVELS)

for distribution and closure of
polylaminate/aluminum/tin foil
capsules or pvc capsules

Production with 4 heads : 4000 bottles per hour
Production with 6 heads : 6000 bottles per hour
Production with 8 heads : 8000 bottles per hour