


STERI-BOOK



SAFELY REMOVE GERMS FROM LIBRARY MATERIALS AT UP TO 6 BOOKS PER MINUTE.

The Steri-book eliminates bacteria, viruses, and mould from library materials with the touch of a button. UV rays are used to disinfect a wide variety of materials including books, magazines, cell phones, purses and writing utensils.

UV lamp



THE STERI-BOOK DISINFECTS BY USING UV-C LAMP WHICH RADIATES A 253.7 WAVE LENGTH. THE RESULT IS THE MOST OUTSTANDING DISINFECTION EFFECT AMONG UV WAVE LENGTHS

Internal circulation



STERI-BOOK USES AN INTERNAL CIRCULATION STRUCTURE WHICH DOES NOT TAKE IN EXTERNAL AIR.

Air blower



REMOVES DUST FROM BOOKS AND KEEPS BOOKS OPEN SO THAT UV LIGHT CAN REACH INSIDE THE BOOK EFFECTIVELY.

Phytoncide deodorant



A NON-TOXIC NATURAL ANTIMICROBIAL DEODORANT MADE WITH 100% NATURAL VEGETAL MATERIAL. IT DEPOSITS ON THE ODOUR MOLECULE AND DECOMPOSES AND PROTECTS FROM SALMONELLA COLON BACILLUS AND STAPHYLOCOCCUS SAFELY WITH ITS STRONG ANTIMICROBIAL EFFECT.

ON/OFF Button

Easy power cut button (located inner front of the disinfecting chamber)

UV-C lamp

Install 10w*8pcs (base on EBS-401)

Semiautomatic Book Holder

Supply semiautomatic book holder that books can easily be plugged in and minimize blind spot to enhance UV sterilizing power.

Travelling Wheel

Convenient to move, fitted with a stopper and can be fixed after installation.



Tempered glass

Apply safety tempered glass to prevent ultraviolet rays from being released externally and be resistant to external shock

Safety switch

Apply safety switch that the disinfection operation is automatically stopped when opening the door during disinfection

Machine room

Main electricity, Fan, Filter, Air freshener

SPECIFICATIONS

Product Size	690(W)*590(D)*1420(H)mm
Color	Black or White
Door Material	Aluminum and Tempered Glass (3.2mm)
Body Material	Aluminum and Steel
Normal Voltage	AC 220V, 50/60Hz
Standby Power	2.5watt
Power Consumption	220watt (Normal)
UV-C Lamp	253.7nm short-wavelength UV-C Lamp 10watt10EA
Filter	Dust Filter, 420(W)*315(H)*10(D)mm, 3EA
Sterilization Time	60 second (Basic) or set time up&down (ratio of 10 second)
Start Botton	Smart touch button
Door Switch	Micro switch
Wheel	Movement wheel and fix

AVAILABLE AT :

Canadian Reseller:

RISTeCh

8-5115 Harvester Rd.

Burlington, Ontario

Phone: 1-905-631-2451

info@ristech.com, www.ristech.com

US Reseller:

Kirtas

749 Phillips Rd.

Victor, New York 14564

Phone: 585-924-2420

Toll-Free: 877-761-0444

jchastang@kirtas.com, www.kirtas.com