



# TD-Channel 95

## Mobile Thermometry Disinfection Channel

- Ultrasonic atomization system
- Body Temperature Detection
- Face & Palm Verification
- Collapsible package



The thermometry and disinfection integrated channel are used for disinfection of body, pet, good and other objects in public space entrance. With body temperature terminal equipped, it is simply to check the passenger temperature.

The whole system is easily operation, it could feed disinfectant liquid automatically, real-time display of running state, automatic reaction of objects entry and exit, easily adjustment for fog quantity and spray time.

Beside above, it is folding designed for easier shipment, and it equips with casters for movement and rapidly deployment.

## Features

- **Ultrasonic atomization system**  
The equipment port is equipped with a microwave sensor, which can sense that someone enters, start the fog maker automatically, spray disinfectant into the channel for a duration of 10S-3 minutes for a duration of 10second to 3 minutes
- **Body temperature detection optional (Device: SpeedFace-V5L[TD])**  
Disinfection channel can be equipped with temperature detection equipment, can be used to measure body temperature remotely without contact, which can effectively avoid cross infection, normal voice prompt of body temperature, voice prompt of overheating alarm of body temperature
- **Smart hand sanitizer sprayer**  
The temperature measuring area is equipped with Smart hand sanitizer sprayer. It has no contact induction spray, is safe and sanitary, and can effectively disinfectate the opponent's part
- **Equalizing spray box, thinning throttling, not damaging facial organs**  
In the disinfection channel, a balanced spray method is adopted, which does not directly spray the human facial organs. The fog is more refined and does not cause waste
- **Lighting auxiliary function**  
Fully considering the use of different scenes, LED waterproof lamp is set in the disinfection channel, which can be used at night or in a dark place
- **Quick layout and transfer function**  
There are four casters and brakes at the bottom of the equipment, which can quickly arrive at the designated place for quick installation

## Specifications

Model	TD-Channel 95
Body temperature detection (Optional)	SpeedFace-V5L[TD]
· Temperature Measurement Distance	30 ~ 50cm (1~ 1.64ft)
· Temperature Measurement Accuracy	±0.3°C (±0.6°F)
· Temperature Measurement Range	34 ~ 45°C (93.2 ~ 113°F)
· Operating Temperature	16°C ~ 32°C (60.8°F ~ 89.6°F)
Disinfectant Capacity	15L
Passage Size	1.8 * 1 * 2.2 m
Voltage	AC220V
Power	400W
Noise	≤ 36 dB
Package Size	1.95m*1.15m*0.85 m
Package Weight	300Kg

## Applied to all kinds of public places



Hospitals



Schools



Communities



Factories



Enterprises & institutions



Constructionsites



Supermarkets



Shoppingmalls



Stations




Airports



Banks



Hotels



KTV



Exhibitions

