
Dome Light Source Series-Dome Light Source




Product Features

- ◆ Similar to the effect of shadowless light source;
- The light shines on the inner wall of the hemisphere and then diffuses on the measured object, making the light more uniform;
- Eliminate the problem of uneven and reflective surfaces on the illuminated object.


Application scope

- ◆Surface and arc defect detection;
- ◆Edge extraction of workpieces;
- ◆Character detection;
- ◆Line detection.


Spectral diagram




Illumination map



Uniformity diagram





Sectional structure diagram



LWD=10mm

LWD=50mm LWD=100mm

Note: This image is only for illustration purposes and may not be identical to the actual product

Wavelength/ Color Temperature	Red (R)	620-630nm	Green (G)	520-530nm				
	Blue (B)	460-470nm	White (W)	6500 ± 500K				
	Infrared (IR)	850/940nm	Ultraviolet (UV)	365-405nm				
Save environment	1	-20~60℃	1	20~80% (non condensing)				
Usage environment	humidity	0~40℃	humidity					
Select accessories	Light source extension cable							
Service life/warranty	When the ambient temperature is 25 °C, the brightness of the light source will decrease by less than 30% after 10000 hours of use (excluding ultraviolet)							
	When the ambient temperature is 25 °C, the 100% brightness of the ultraviolet light source will decay by less than 30% after 1000 hours of use							
	Within one year of shipment, if there is a malfunction due to non-human factors, free repair or replacement services will be provided							

Application case of dome light source




analyte



Lighting diagram



>>>



Content	Character detection for vacuum packaging bags
Tested item	packing bag
Difficulties in the plan	The surface of the packaging bag is uneven
Application	KCS-CKH-175-W
Light sourceresult	Clear character imaging and error free character recognition




Imaging rendering




Software processing rendering

Serial	Model	Voltage	Power		Weight (g)
number	Wiodei		R	G/B/W	Weight (g)
1	AIRON-DOME-65	24	4	5	100
2	AIRON-DOME-80	24	6	6.4	160
3	AIRON-DOME-100	24	8	10	250
4	AIRON-DOME-120	24	9	11.6	300
5	AIRON-DOME-150	24	11	14	370
6	AIRON-DOME-175	24	12	18	450
7	AIRON-DOME-210	24	14	20	640
8	AIRON-DOME-240	24	16	24	760
9	AIRON-DOME-275	24	20	28	840
10	AIRON-DOME-320	24	22	32	900
11	AIRON-DOME-350	24	24	35	940
12	AIRON-DOME-400	24	28	40	990







3 AIRON-DOME-100 4 AIRON-DOME-120




5 AIRON-DOME-150 6 AIRON-DOME-175




7 AIRON-DOME-210 8 AIRON-DOME-240





9 AIRON-DOME-275







10 AIRON-DOME-320





11 AIRON-DOME-350





12 AIRON-DOME-400

