HANDHELD FUNDUS CAMERA

## OPT MED LUMO

**Capturing Health** 



Intuitive User
Experience



High-Quality Optics



Seamless Integration



Data Security



# **Early Detection with AI-Powered Handheld Imaging**

Optomed handheld fundus cameras provide access to a variety of essential health data and enable early detection.

The Optomed Lumo® with integrated AI delivers a streamlined workflow for screening, from patient data management to AI result delivery.



### **Retinal imaging**

Fast 50-degree image capture without dilation.



#### Al analysis

Instant result delivery to the camera and Optomed Portal.



#### **Results integration**

Report and image integration with hospital systems.

1-Minute On-the-Spot Screening

### **Reach Patients Anywhere**

#### **Optomed Lumo provides maximum portability**

Image capture, data transfer, Al analysis, and device charging can all be done on-the-go. The optional Optomed Travel Pack allows traveling light with the camera.



#### Designed to be used by any healthcare professional

Optomed Lumo provides an effective diagnostic tool for various purposes from large-scale eye screenings and primary care to emergency room diagnostics and pediatric retinal examinations.



#### Adapts to different healthcare settings

Optomed Lumo sets a new standard for flexibility in retinal screening with its programmable workflows, intuitive user guidance and wireless DICOM connection, both as a handheld and a stationary camera.



## Effective, Reliable, Fast, and Secure Retinal Imaging



#### **Intuitive User Experience**

User programmable workflows, a large touchscreen and a variety of automatic imaging functions enable fast camera operation and image capture.

Intuitive user guidance empowers imaging by any healthcare professional.

Programmable Imaging Sequences

**Intuitive User Guidance** 

Large 5" Touchscreen

Smart Autofocus™



**USB and WLAN** 

DICOM

Cloud Connection for Al services



#### **Seamless Integration**

Wireless DICOM connection ensures seamless image and patient data integration with hospital PACS systems.

High speed USB and WLAN connections ensure fast data transfer to medical records and to the Optomed mobile application.

On-the-spot image analysis with selected Al algorithms is enabled by the camera's cloud connection.



#### **High-Quality Optics and Design**

High-Contrast Optical Design™ allows detecting even the small early-phase retinal changes, with a 50° field of view.

Non-mydriatic imaging complemented with a 12 MP low-noise sensor produces image quality that you need to see.

Non-Mydriatic

12 MP Resolution

50° Field of View

High-Contrast Optical Design™

**Data Encryption** 

**User Authentication** 

**PIN Code Protection** 



#### **Data Security**

Health data is properly protected with AES-256 encryption, PIN code protection, and user authentication implemented in the camera.





Optomed Plc | Yrttipellontie 1, 90230 Oulu, Finland | sales@optomed.com www.optomed.com