

DAC 150.3 SP / DAC 250.3 SP

Hauschild Engineering pioneered dual asymmetric centrifugal technology 50 years ago. Since then, Hauschild SpeedMixer® bladeless lab mixers have become a staple in R&D labs and production facilities around the world. Other companies manufacture or distribute bladeless mixers, but nothing compares to the quality, accuracy and reliability of a Hauschild SpeedMixer®. It's an investment that pays off at every turn.




Technical Data

Specification	DAC 150.3 SP	DAC 250.3 SP
Mixing capacity (g/lb.)	Up to 150 / 0,33 ¹	Up to 250 / 0,55 ¹
Mixing volume (ml/gal)	Up to 250 / 0,06	Up to 500 / 0,13
Mixing Speed (rpm)	300 ÷ 3500	300 ÷ 2500
Mixing time (min.)	10	10
Display	3.5" Touchscreen	3.5" Touchscreen
Internal light	No	No
Programs	100	100
Mixing steps/program	5	5
Vacuum	No	No
Minimum pressure (mbar)	N.A.	N.A.
Vacuum pump	N.A.	N.A.
Voltage - Frequency	230 / 50-60 or 115 / 50-60	230 / 50-60 or 115 / 50-60
Input Power KW	0,95	0,95
Hight Open lid (mm/inches)	720 / 28,3	720 / 28,3
Hight - Closed lid (mm/ inches)	465 / 18,3	465 / 18,3
Width (mm/ inches)	305 / 12	305 / 12
Depth (mm/ inches)	405 / 15,9	405 / 15,9
Weight (kg/lb.)	35 / 77	35 / 77

¹ Including material, jar, and holder when applicable.

Hauschild GmbH & Co. KG

Waterkamp 1
59075 Hamm, Germany
+49-2381-482050
info@hauschild-speedmixer.com



Hauschild SpeedMixer Inc.

37735 Enterprise Ct - Suite 300
Farmington Hills, MI 48331
+1-877-SPDMXER
info.us@hauschild-speedmixer.com