

DAC 400.1 FVZ LR / DAC 400.2 VAC-P LR

Hauschild Engineering pioneered dual asymmetric centrifugal technology 50 years ago. Since then, Hauschild SpeedMixer® bladeless lab mixers have become a staple in R&D labs and production facilities around the world. Other companies manufacture or distribute bladeless mixers, but nothing compares to the quality, accuracy and reliability of a Hauschild SpeedMixer®. It's an investment that pays off at every turn.



Technical Data

Specification	DAC 400.1 FVZ LR	DAC 400.2 VAC-P LR
Mixing capacity (g/lb.)	Up to 400 / 0,88 ¹	Up to 400 / 0,88 ¹
Mixing volume (ml/gal)	Up to 1000 / 0,26	Up to 1000 / 0,26
Mixing Speed (rpm)	800 ÷ 2300	800 ÷ 2300
Mixing time (min.)	10	10
Display	5.9" Touchscreen	5.9" Touchscreen
Internal light	No	Yes
Programs	20	20
Mixing steps/program	5	5
Vacuum	No	Yes
Minimum pressure (mbar)	N.A.	0
Vacuum pump	N.A.	External
Voltage - Frequency	230 / 50-60 or 115 / 50-60	230 / 50-60 or 115 / 50-60
Input Power KW	1,2	1,2
Hight Open lid (mm/inches)	960 / 37,7	1030 / 40,5
Hight - Closed lid (mm/ inches)	640 / 25,1	730 / 28,7
Width (mm/ inches)	440 / 17,3	440 / 17,3
Depth (mm/ inches)	640 / 25,1	640 / 25,1
Weight (kg/lb.)	76 / 167	96 / 211

¹ Including material, jar, and holder when applicable.


Hauschild GmbH & Co. KG

Waterkamp 1

59075 Hamm, Germany

+49-2381-482050

info@hauschild-speedmixer.com



Hauschild SpeedMixer Inc.

37735 Enterprise Ct - Suite 300

Farmington Hills, MI 48331

+1-877-SPDMXER

info.us@hauschild-speedmixer.com