



ARBARR ELECTRONICS LTD.

# AVIATION GROUND SUPPORT

PRODUCT GUIDE: THE S.E.A.L. WAND





# INTRODUCTION

- Arbarr Electronics is an award winning, ISO:9001: 2008 company, with over 30 years of experience in the lighting industry.
- Arbarr envisages the need for cost effective, environmentally friendly and innovative solutions to your lighting requirements.
- Our customer base includes the Queen's Flight (UK), the Queen's Helicopter Flight (UK), the BAA (the largest airport group in the world), DHL, FedEx, U.S.A.F. (Okinawa), Jackie Stewart's F1 Racing Team, several regional and International Airports, as well as many local government Fire and Police departments.
- Due to the multi-functional nature of Arbarr's products, they are ideally suited to any application where emergency lighting (helipad marking, obstruction marking, etc) or marshalling (both air and road traffic), is required.
- Arbarr's products have been used in both civil and military operations (IR & NVG), providing both permanent and temporary solutions to your lighting needs, complying with relevant CAA, FAA and ICAO specifications, ensuring quality that is second to none.



Our Head Office and factory is located just outside of Limavady on Northern Ireland's stunning North Coast.





# THE S.E.A.L. WAND



- The S.E.A.L. Wand is a rechargeable, multi intensity, marshalling wand.
- With a range of lens sleeves available including covert lenses, the S.E.A.L. Wand can be used for road traffic, aircraft and military marshalling.
- The S.E.A.L. Wand may be charged using plug top or vehicle cigar lighter socket (optional).
- The mains charger allows up to two S.E.A.L. Wands to be charged simultaneously. Full charge, from empty, is achieved in approximately two hours.
- A carry case is also available to store a pair of wands, charger and up to six lens sleeves.
- Various types of lenses are available for the S.E.A.L. Wand including: orange, red, clear, blue, NVG and IR. Custom colours are available on request.

# SPECIFICATIONS

The tables below show the relevant specifications regarding dimensions, approximate battery life and and intensity of the S.E.A.L. Wand.

Setting	Luminosity (Candela +/- 5)	Battery Life (Hrs)
1	100	2
2	60	4

*Approximate luminosity and battery life*

Width (mm)	Height (mm)	Weight (Kg)
115	430	0.5

*S.E.A.L. Wand dimensions*



**Further products including the  
Arbarr Marshalling Bat are available.  
For more information, please contact us.**

**Arbarr Electronics**  
Unit 3, Aghanloo Industrial Estate,  
Limavady, BT49 0HE

**028 7776 6611**

[enquiries@arbarr.co.uk](mailto:enquiries@arbarr.co.uk)