



# Product Portfolio





# Excellence without exception

At Starkey, we are committed to helping you help your patients hear and live their best lives — through the most innovative technology, highest quality products, industry-best customer service, and delivery you can rely on.

**It's excellence without exception,  
and it's our promise to you.**



# OMEGA<sup>AI</sup>



mRIC R  
Waterproof Wireless Rechargeable LED

RIC RT  
CROS COMPATIBLE  
Waterproof Wireless Rechargeable LED

RIC 312  
CROS COMPATIBLE  
Waterproof Wireless Rechargeable LED

CIC  
Waterproof Wireless Rechargeable LED

ITC R  
Waterproof Wireless Rechargeable LED

ITE R  
Waterproof Wireless Rechargeable LED

Waterproof\* Wireless Rechargeable LED Status Indicator Light

\*Up to 1m.

## Wireless Accessories



StarLink Edge Remote Microphone

StarLink Edge Table Microphone

StarLink Edge TV Streamer  
AURACAST

StarLink Remote Control 2.0


## Available Colours

Standard Colours	<input type="radio"/> White	<input type="radio"/> Chestnut	Faceplate Colours	<input type="radio"/> Pink	<input type="radio"/> Chestnut	Shell Colours	<input type="radio"/> Clear	<input type="radio"/> Blue/Red
	<input type="radio"/> Tech Black	<input type="radio"/> Caramel		<input type="radio"/> Light Brown	<input type="radio"/> Dark Brown		<input type="radio"/> Pink	<input type="radio"/> Black
	<input type="radio"/> Graphite Gray	<input type="radio"/> Beige		<input type="radio"/> Medium Brown	<input type="radio"/> Black		<input type="radio"/> Light Brown	
	<input type="radio"/> Silver							

## SnapFit 2.0 Stock and Custom Cased Receivers

Comfort Bud Open 5 mm, 6 mm, 7 mm, 9 mm, 11 mm	Comfort Bud Occluded 4 mm, 5 mm, 6 mm, 7 mm, 9 mm, 11 mm	Power Dome 8-10 mm, 10-12 mm, 12-14 mm	Custom Cased Receiver Custom shell with embedded receiver	Stock Silicone Helix RIC Earmold	Stock Hollow Silicone RIC Earmold	Stock Silicone RIC Earmold

## Fitting Ranges



Engineered with our industry-leading AI, our G3 Gen AI Neuro Processor, and the world's first DNN-powered directionality system, DNN 360, all-new Omega AI is Starkey's most advanced hearing technology yet. It's designed to come closer to restoring the normal sense of hearing than any hearing technology before it.

## OMEGA<sup>AI</sup>

Tech Tiers | Channels | Bands

24

20

16

	24	20	16
<b>Edge Mode+</b>			
Automatic & User Control Personalisation App Control	●●●	○●○	○●○
<b>Speech Optimisation</b>			
Consonant Brightness Voice AI*	●	○	○
<b>ENHANCED Sound Manager</b>			
DNN 360	DNN Directionality**	●	○
	DNN Spatial Awareness**	●	○
Quiet	Maximum expansion	Moderate expansion	Mild expansion
Machine Noise Reduction	Up to 22 dB of reduction	Up to 12 dB of reduction	Up to 7 dB of reduction
Speech in Noise Reduction	Up to 22 dB of reduction	Up to 10 dB of reduction	Up to 8 dB of reduction
Transient Noise Reduction	Up to 15 dB of reduction	Up to 9 dB of reduction	Up to 6 dB of reduction
Wind Reduction	Up to 35 dB of reduction	Up to 19 dB of reduction	Up to 10 dB of reduction
<b>Additional Key Features</b>			
Gen AI Smart Assistant & TeleHear AI Translate Transcribe	●	○	○
Multiflex Tinnitus Pro Smart Assistant 2-Way Audio	●●●	○●○	○●○
Hearing Health & Activity Tracking Fall Alert & Balance Assessment Reminders & Self Check	●●●	●●●	●●●
Auto Sleep Tap Control	●●●	●●●	●●●
TeleHear full remote fit REM Target Match Demo Stream	●●●	●●●	●●●

## Charging Solutions

All chargers include Turbo Charge



StarLink Premium Charger 2.0 w/ onboard battery  
• mRIC R / RIC RT



StarLink Charger 2.0  
• mRIC R / RIC RT



StarLink Premium Custom Charger 2.0 w/ onboard battery  
• ITC / ITE R



StarLink Custom Charger 2.0  
• ITC / ITE R

## Compatible Apps

My Starkey HearShare

Scan to check phone compatibility



Features noted above in blue are available within My Starkey app.

\*For iOS users only. \*\*RIC styles only.

# GENESIS<sup>AI</sup>



## Wireless Accessories



Waterproof\* Wireless Rechargeable

\*Up to 1m.


## Available Colours

<b>Standard Colours</b>	<input type="radio"/> White	<input type="radio"/> Chestnut	<b>Faceplate Colours</b>	<input type="radio"/> Pink	<input type="radio"/> Chestnut	<b>Shell Colours</b>	<input type="radio"/> Clear	<input type="radio"/> Blue/Red
	<input type="radio"/> Tech Black	<input type="radio"/> Caramel		<input type="radio"/> Light Brown	<input type="radio"/> Dark Brown		<input type="radio"/> Pink	<input type="radio"/> Black
	<input type="radio"/> Graphite Gray	<input type="radio"/> Beige		<input type="radio"/> Medium Brown	<input type="radio"/> Black		<input type="radio"/> Light Brown	
	<input type="radio"/> Silver							

## SnapFit 2.0 Stock and Custom Cased Receivers

<b>Comfort Bud Open</b> 5 mm, 6 mm, 7 mm, 9 mm, 11 mm	<b>Comfort Bud Occluded</b> 4 mm, 5 mm, 6 mm, 7 mm, 9 mm, 11 mm	<b>Power Dome</b> 8-10 mm, 10-12 mm, 12-14 mm	<b>Custom Cased Receiver</b> Custom shell with embedded receiver	<b>Stock Silicone Helix RIC Earmold</b>	<b>Stock Hollow Silicone RIC Earmold</b>	<b>Stock Silicone RIC Earmold</b>

## Fitting Ranges



## GENESIS<sup>AI</sup>

Tech Tiers | Channels | Bands

12

<b>Edge Mode+</b>	Automatic	<input type="radio"/>
	User Control	<input type="radio"/>
	Personalisation	<input type="radio"/>
	App Control	<input type="radio"/>
<b>Speech Optimisation</b>	Consonant Brightness	<input type="radio"/>
	Voice AI*	<input type="radio"/>
<b>Sound Manager</b>	Quiet	<input type="radio"/> Mild expansion
	Machine Noise Reduction	<input type="radio"/> Up to 7 dB of reduction
	Speech in Noise Reduction	<input type="radio"/> Up to 8 dB of reduction
	Transient Noise Reduction	<input type="radio"/> Up to 6 dB of reduction
	Wind Reduction	<input type="radio"/> Up to 10 dB of reduction
<b>Additional Key Features</b>	Translate	<input type="radio"/>
	Transcribe	<input type="radio"/>
	Multiflex Tinnitus Pro	<input type="radio"/>
	Smart Assistant & Find My Hearing Aids	<input type="radio"/>
	2-Way Audio	<input checked="" type="radio"/>
	Hearing Health & Activity Tracking	<input checked="" type="radio"/>
	Fall Alert	<input checked="" type="radio"/>
	Reminders & Self Check	<input checked="" type="radio"/>
	Auto Sleep	<input checked="" type="radio"/>
	Tap Control	<input checked="" type="radio"/>
	TeleHear full remote fit	<input checked="" type="radio"/>
	REM Target Match	<input checked="" type="radio"/>
	Waterproof up to 1m**	<input checked="" type="radio"/>
	Apple Watch Controls*	<input checked="" type="radio"/>

## Charging Solutions

All chargers include Turbo Charge



StarLink Premium Charger 2.0 w/ onboard battery

• mRIC R / RIC RT



StarLink Charger 2.0

• mRIC R / RIC RT



StarLink Premium Custom Charger 2.0 w/ onboard battery

• ITC / ITE R



StarLink Custom Charger 2.0

• ITC / ITE R

## Compatible Apps



My Starkey



Scan to check phone compatibility



Genesis AI marked a new beginning for hearing technology by introducing the industry to the most advanced processor technology with a unique onboard Deep Neural Network (DNN) accelerator. This Neuro Sound Technology in Genesis AI is designed to deliver sound so transparent and true to life, patients will forget they're wearing hearing aids.

Features noted above in blue are available within My Starkey app.

\*For iOS users only. \*\*Rechargeable styles only.



# Signature SERIES



IIC NW

CIC NW

CIC R NW

Waterproof Rechargeable

\*Up to 1m.

## Available Colours

**Faceplate Colours**


**Custom Colours**

- Pink
- Light Brown
- Medium Brown
- Chestnut\*
- Dark Brown
- Black

**Shell Colours (IIC only available in Black)**

- Clear
- Blue/Red
- Pink
- Black
- Light Brown

## Fitting Ranges



Visit [StarkeyPro.co.uk/products/hearing-aids/signature-series](https://www.starkeypro.co.uk/products/hearing-aids/signature-series) for full technical data sheets.



Based on the industry's most advanced processor and powered by our industry-leading Neuro Sound Technology, Starkey Signature Series deliver the size, performance and personalised fit that patients can only get from you.

Tech Tiers   Channels   Bands	24	20*	16*
<b>Edge Mode+ (CIC styles only)</b>			
User Control	●	○	○
<b>Speech Optimisation</b>			
Consonant Brightness	● Maximum	● Mild	● Mild
<b>Sound Manager</b>			
Quiet	●●● Maximum expansion	●● Moderate expansion	●● Mild expansion
Machine Noise Reduction	●●● Up to 22 dB of reduction	●● Up to 12 dB of reduction	● Up to 7 dB of reduction
Speech in Noise Reduction	●●● Up to 22 dB of reduction	●● Up to 10 dB of reduction	● Up to 8 dB of reduction
Transient Noise Reduction	●●● Up to 15 dB of reduction	●● Up to 9 dB of reduction	● Up to 6 dB of reduction
Wind Reduction	●●● Up to 35 dB of reduction	●● Up to 19 dB of reduction	● Up to 10 dB of reduction
<b>Additional Key Features</b>			
Multiflex Tinnitus Pro with new tinnitus maskers	●	●	○
REM Target Match	●	●	●
Waterproof**	●	●	●

\*CIC styles only. \*\*Up to 1m. Rechargeable style only.

## Charging Solutions

All chargers include Turbo Charge



StarLink Premium Custom Charger 2.0 w/ onboard battery

• CIC R NW



StarLink Charger 2.0

• CIC R NW



# Wireless Accessories

Our accessories, paired with our wireless hearing aids, connect to your favorite music, TV shows, and phone calls with superior sound quality.

Enabled with Bluetooth® technology, they are easy to pair and even easier to use.



# My Starkey App

Easy as it gets. Powerful as you need.

Designed with the input of hearing aid wearers, My Starkey pairs with our hearing aids to help your patients enjoy greater listening moments, improved well-being, and easier everyday living – all from the palm of their hand or wrist with Apple Watch compatibility.




## My Starkey

		Compatibility	
		OMEGA <sup>AI</sup>	GENESIS <sup>AI</sup>
StarLink EDGE	 <b>EDGE TV Streamer</b> Uses Bluetooth® Low Energy (LE) Audio protocol to stream audio straight from a TV to paired LE Audio-enabled hearing aids.	●	○
	 <b>EDGE Remote Microphone</b> Enjoy one-on-one conversations in noise. Instantly starts/stops streaming the second it's powered on or off.	●	○
	 <b>EDGE Table Microphone</b> Eight built-in microphones help you hear whoever is speaking by streaming their voice directly to your hearing aids.	●	○
StarLink	 <b>Remote Control 2.0</b> Easily control memory and volume, mute hearing aids and turn other special features on and off.	●	●
	 <b>TV Streamer</b> Allows patients to easily stream audio from their TV or other electronic audio source directly to their hearing aids.	○	●
	 <b>Table Mic</b> A multi-functional device designed to improve listening in group gatherings or noisy restaurants. It also functions as a TV streamer or even a bodyworn remote microphone.	○	●
	 <b>Remote Mic +</b> Enables easy audio streaming and one-on-one conversations in noisy environments.	○	●
	 <b>Mini Remote Mic</b> Patients can enjoy one-on-one conversations in noisy environments by attaching it to a conversation partner's clothing.	○	●

## Focus on benefits

Omega AI and Genesis AI wireless hearing aids can connect via Bluetooth® technology to the My Starkey app.

- Hear better anywhere**  
 Make instant adjustments for clearer speech and reduced noise – even in the toughest listening environments.
- Get tips, tools, and resources**  
 Adapt to hearing aids faster with quick how-to's, tips, and videos. All tailored for where the hearing aid wearer is on their hearing journey.
- Monitor health and wellness**  
 Monitor daily hearing and physical activity to help stay healthy. Set and achieve goals for hearing, steps, exercise, and beyond.
- All from the palm of your hand or wrist**  
 Change programs and adjust volume quickly and easily on a compatible Apple Watch. Visit the Learn section within My Starkey or installation instructions.



## How to download

- Open the **App Store**  on Apple devices or **Google Play**  on Android devices.
- In the search box, type **My Starkey**.
- Tap **GET** on Apple devices or **INSTALL** on Android devices. This will download the app to the compatible device.




## Other Apps

### Hear Share

Works with My Starkey or Thrive apps to allow wearers of Omega AI, Edge AI, and Evolv AI to:

- Share information about hearing aid usage, social and physical activity progress, safety, and more—with the people they choose.
- Provide peace of mind for patients and their caregivers.





Learn more about Starkey  
products at [StarkeyPro.co.uk](https://StarkeyPro.co.uk)



Starkey logo, Starkey, TeleHear, Starkey Edge, Edge Mode, Multiflex Tinnitus, StarLink, Starkey Signature Series, SoundGear Shield, Omega, Sound [+checkmark], Genesis, Hear Share, Evolv, Thrive, SoundGear logo, SoundGear, Phantom, Hearing is Our Concern, Hear better. Live better. and Tunz are trademarks of Starkey Laboratories, Inc.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The Auracast™ word mark and logos are trademarks owned by the Bluetooth SIG. Any use of such marks by Starkey is under license. Other trademarks and trade names are those of their respective owners.

Apple Watch is a trademark of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. "Made for iPod," "Made for iPhone" and "Made for iPad" mean that an electronic accessory has been designed to connect specifically to iPod, iPhone, or iPad, respectively, and has been certified by the developer to meet Apple performance standards. Apple is not responsible for the operation of this device or its compliance with safety and regulatory standards. Please note that the use of this accessory with iPod, iPhone, iPad or Apple Watch may affect wireless performance. Google Play Store is a trademark of Google, LLC.