



Safety Glasses Policy and Procedure

For a member to be eligible for MOST Safety Glasses they must follow these guidelines.

- Have an eligible status on the MOST Boilermaker Delivery System (MBDS)
- Have a current prescription within the last two years
- Member can order glasses every six months as long as they meet all the above requirements. If a member needs a new pair before the six months period they are available for purchase. Please note lost or stolen glasses are not covered by MOST.
- All payments must be submitted through money order. We do not accept personal checks or credit card information.

Please read and follow all instructions listed below in order to process your request for safety glasses as quickly as possible.

- 1) Contact MOST with the type of frame you would like. MOST will then send you a tester frame and prescription form.
- 2) Take the safety glass frame and the prescription form to your eye doctor. Ask your doctor to complete the form with your prescription and measurements. It is VERY important to have ALL the measurements from the doctor on the form. **If the prescription form is received incomplete, it will be returned to you and it will delay the processing of your glasses. DO NOT attach a copy of your prescription to the MOST form.** Your prescription **must** be on the MOST prescription form in order to process your request.
- 3) Please select either clear **or** 20% tint for the type of lens you would like.
- 4) If you choose to have **transition lenses** or **anti-reflective coating** made to your glasses, please be aware that these items are considered "additional" and are NOT covered by MOST. Please enclose a **money order** payable to MOST. **Do NOT send a personal check** or it will be returned to you. **See the back of this form for current prices.** Your order will NOT be processed without payment. Please write "Transitions" and/or "Anti-reflective coating" in the Special Instructions box on the form.
- 5) Check the pre-printed information at the bottom of the prescription form. If any information has changed, please make the proper corrections. Please note this is the address the lab uses for mailing your glasses, so it is important this info is correct. **Sign your name by the "X" on the bottom of the form to verify all information is correct.**
- 6) Return the tester frames and the completed prescription form in the shipping carton. Send to MOST for processing with the provided mailing label and pre-paid postage.
- 7) Glasses will be mailed to the address on the form approximately 7 - 10 business days AFTER your order is received at the lab.

Frame Style	Transition Price	Anti-Reflective Coating
OnGuard 220FS	\$35.00	\$30.00
OnGuard 220	\$37.00	
Titmus SW07	\$37.00	
Hudson H-1	\$42.00	
Dust Buster	\$42.00	

If a member wants to purchase an additional pair follow this pricing guideline

<u>Dust Buster and H1</u>	<u>Clear</u>	<u>Transitions</u>
Single Vision	\$40	\$82
Bifocal	\$54	\$96
Trifocal	\$64	\$106
Progressive	\$87	\$126
Varilux Progressive	\$125	\$158
Double Seg	\$87	NA

<u>Titmus SW07 and 220</u>	<u>Clear</u>	<u>Transitions</u>
Single Vision	\$54	\$91
Bifocal	\$68	\$105
Trifocal	\$78	\$115
Progressive	\$101	\$138
Varilux Progressive	\$134	\$171
Double Seg	\$101	NA

<u>220FS</u>	<u>Clear</u>	<u>Transitions</u>
Single Vision	\$64	\$99
Bifocal	\$78	\$113
Trifocal	\$88	\$123
Progressive	\$111	\$146
Varilux Progressive	\$144	\$179
Double Seg	\$111	NA

You will be provided with a tester frame that you choose from the list below and a prescription order form to take to your personal eye care professional to complete with your prescription and measurements. **MOST is not responsible for any costs incurred in obtaining the prescription.** Call the MOST office (1-800-395-1089) or fax your order in (913-281-0037). **This is not the prescription form so please do not send your prescription with this request form.**

Hudson H-1



Hudson H-1

- Black/Orange color – size 56-20-130
- Non-Conductive
- Soft, Adjustable nose pads
- Removable foam Brow Protection
- Built in top and side shield protection
- Meets ANSI Z87.1 Standard

OnGuard 220



OnGuard 220

- Black Nylon frame
- Removable dust dam included
- Flex finger bridge conforms to any nasal profile
- Contemporary, sports styling with integrated side protection
- Meets ANSI Z87.1 Standard


Dust Buster



Dust Buster

- Small frame and dual lens adaptable to wide range of Rx's
- Telescoping temples to maximize comfort and fit
- Foam Elemental Deflectors seal eye region from airborne particles
- Meets ANSI Z87.1 Standard

OnGuard 220FS



OnGuard 220FS

- Black Nylon Frame
- Non-Conductive
- Flex finger bridge conforms to any nasal profile
- Removable full eye seal protects against dust and dirt in extreme conditions
- Indirect venting improves airflow and reduces fogging
- Black adjustable head strap
- Meets ANSI Z87.1 Standard

Titmus – SW07



Titmus – SW07

- Nylon-based material withstands high heat and chemicals.
- Removable/replaceable closed cell foam insert (covers whole eye)
- Multi-sized nose pads, adjustable strap, and regular temple options
- Face-form wrap for enhanced coverage
- Extended and integrated side shield design
- Meets ANSI Z87.1 Standard

Please select a frame style from above. Complete your request by calling (1-800-395-1089 ext. 325), Faxing (913-281-0037) or Mailing this form to the MOST office.

First Name: _____ Last Name: _____

Address: _____

City, State, Zip: _____

Home Phone: _____ Home Local: _____ Date of Birth: _____

Social Security Number: _____