Hethon control

You can equip our Feeders with a separate control.

This way you can easily control multiple Feeders simultaneously and even add other devices to your Feeder-configuration.



Loss in Weight - Gain in Weight

Hethon dosing machines can be placed a weighing plateau with one or more built-in loadcells as you require. In combination with the software you can, as such, create a high-quality dosing system with many adjustment options. You can, for instance, apply pre-set formulas, adjustable dosing speeds, or a coarse and fine dosing for even more accuracy.

Do you want to try the feeder?

You can rent the Hethon Feeder, with or without control. When you decide to purchase, the rental costs that you incur during the first week expire.

Would you prefer to test your material on our location?

We have a test room and can test whether our application is also suitable for you. Contact us to discuss your question: we are ready for you!



CONTACT

Hethon Nederland B.V.

Vlijtstraat 47/49

7005 BN Doetinchem


The Netherlands

T +31 (0)74 250 05 55

E info@hethon.nl

HETHON FI FXIBI F WALL FEEDERS

For a perfectly dosed flow of dry materials




www.hethon.nl www.hethon.nl www.hethon.nl

HETHON - Feeder technology

Conventional solution:

STIRRING ARMS AND SCREWS


The dry substances you work with, sometimes don't have a natural flow. The accurate dosing of these substances is therefore often a challenge.




The Hethon solution:

FLEXIBLE WALL HOPPER

Hethon dosing machines are equipped with a Flexible Wall Hopper and by massaging the wall hopper walls, the material is transported smoothly towards the dosing screw. As the mechanical paddles are not inside the wall hopper, as opposed to the stirring arms and screws, the dry material will not get damaged and ratholing or bridging is prevented.



The Flexible Wall Hopper is easily detachable!



Your benefits of a Hethon Feeder

- Prevent ratholing, bridging and damage to the material
- Minimal power consumption
- Easy to clean due to detachable components
- Low-maintenance because of few wear points
- Stable and strong thanks to high-quality lnox tube frame construction
- Separate paddle propulsion possible
- Limited segregation
- 4 easily detachable doors
- Steel profile cast in the hopper for stable retrieval
- Hopper available in 5 versions
- Very few contact elements
- Excellent price-performance ratio

A Flexible Wall Hopper for every application

For every application there is a Flexible Wall Hopper with the appropriate specifications. The easily detachable dosing hoppers can, as an exchange hopper, be conveniently stored elsewhere.



Extra Hethon nozzles

The Hethon Feeders come standard with an open nozzle. In our option-assortment you can also find a range of other nozzles, for example horizontal or vertical T-nozzles with or without valves, for controlled product dosing. In order for this application to apply: easy and quick to remove and to clean, we developed the T-Nozzle door.

Widely used in large, professional industries worldwide

www.hethon.nl