

DLI P/N	OEM P/N	DESCRIPTION	MODEL
LMP-12528		LAMP	SPTL
LMP-16513	9908-04-1205	LAMP	V-BEAM
LMP-16509	9908-17-0408	LAMP	GENTLELASE (all)
ROD-18036		ROD/Alex	GL, GLP, MGL
ROD-18046		ROD	MGY
FLT-17223		FLOW TUBE	GENTLELASE (all)
LPR-17384	8010-00-0050	DISTANCE GUAGE WINDOW (755 only)	
LPR-17854		DISTANCE GUAGE WINDOW (1064 only)	
		DISTANCE GUAGE WINDOW (1064 and 755)	
		Vbeam slider lenses	

LPR-18070		DYE window 5/Pack	
YFL-18123	8050-05-1520	DYE LENS 10 MM #1	
YFL-18124	8050-05-1540	DYE LENS 10MM #2	
YFL-18125	8050-05-1530	DYE LENS 7 MM #1	
YFL-18126	8050-05-1550	DYE Lens 7MM #2	
YFL-17386	8050-00-1520	755 LENS, UNCOATED	Slider Optics 12,15,18
YFL-17387	8050-00-1540	755 LENS, COATED	Slider Optics 12,15,18
LPR-17385	8010-00-0050 / LPR-17384, but sapphire	Sapphire Window @ 755	Slider or Distance Gauge
ORI-17406		O-RING FOR 8010-00-0050	Distance Gauge O-Ring
	8050-00-0010	Fiber Focusing Lens/755nm	MGL/GL/GLP

		Fiber Focusing Lens/1064nm	MGYag
	7121-00-9310	DISTANCE GAUGE 12MM	
in process	7121-00-9320	DISTANCE GAUGE 15MM	GentleLase / GentleYag
in process	7121-00-9100	DISTANCE GAUGE 18MM	GentleLase / GentleYag
in process		Handpiece/Slider Cover	GENTLELASE (all)
FLT-17775		TRIPLE BORE	GENTLELASE (all)
		DYE KIT	V-BEAM
		Barium Powder for Head (GentleLase/yag)	
BMD-17904		Fiber	GLP
		Fiber	MGL (6/8/10)

		Fiber	MGL (12/15/18)
		Fiber	MGY (1.5/3)
BMD-18240		Fiber	MGY (6/8/10)
BMD-18241		Fiber	MGY (12/15/18)
		Delivery System	GLP
		Delivery System	MGL (6/8/10)
		Delivery System	MGL (12/15/18)
	7122-00-3634	Delivery System	MGY (1.5/3)
		Delivery System	MGY (6/8/10)
		Delivery System	MGY (12/15/18)
	7122-00-7395		Yag Fiber
	8050-00-0520	Window for Yag Slider Cap	MGY

	8050-00-0540		MGY
		Cryogen Valve re-build	
		Cryogen Valve Oring Kit	
	7122-00-3349	Cryogen Valve New	
		GL Head w/o Lamps or Rod	
WFI-17907		Water Pump	
WFI-17908		DI Filter	
EYE-NS200		Eyewear	
	1510-00-0080	Capacitor	GLP
	5103-00-0030	Footswitch	

	7111-00-2684	, HV CONT.PCB, VPYAG	
	7111-00-2683	, HV PCB, VPYAG	
		HVPS GL	
		HVPS GLP	
	4001-01-0076	HVPS MGL	
	4001-01-0078	HVPS MGY	
	7111-00-2630		
	7122-00-3290		
	3455-31-0060	HTR,CRTG, 1000W/120240V	MGY
	7122-57-3497	Refurb. Laser Head	MGY
	7111-00-2660	Assy, BOM, HP PCB	MGY
	7111-00-2682	AC Distribution Board	MGY

	4001-01-0078	HVPS	MGY
	4820-00-0081	IGBT Module, 1200V/600A	MGY
	7122-00-3454	Lens Cap 12/15/18	MGY
	7122-00-3497	Laser Head	MGY
	8901-01-1342	FSE, HVPS	MGY
	7122-00-3300	Fiber receptacle	MGY
	7122-00-3795	Fiber	MGY
	7122-00-8507	delivery System w/o fiber 12/15/18	MGY
	7122-00-3792	Delivery System 12/15/18	MGY
	3160-06-0002	Lamp O-ring	MGY
	7122-00-3165	DI Filter	MGL

	3160-01-0012	Lamp O-ring	MGL
	7122-00-3348	DI Pump	MGL
	5650-40-0450	Inductor Foil, 450uH, L2	MGL
	8050-00-0010	Fiber Focus Lens	MGL
	7122-00-7551	Delivery System 10/12/15	MGL
	4001-01-0076	HVPS	MGL
	3412-14-0605	Plug, DYE Pump to Res	MGL
	7121-57-6700	Refurb. Laser Head	MGL
	7111-00-2610	Assy, PCB, AC Distr.	MGL
	1301-00-8056	End Cap	MGL
	5650-45-0750	Inductor Foil, 750uH, 45A	MGL
	5650-20-0300	Inductor Foil, 300uH, 20A	MGL

	8901-01-1332	FSE, 4001-01-0076 HVPS	MGL
	7111-00-2660	Assy, BOM, HP PCB	MGL
	7122-00-3349	DCD Valve/Cryogen	MGL
	7122-00-3351	12/15/18 End Cap	MGL
	8901-01-1341	FSE, 7111-00-2610, PCB AC Dist.	MGL
	7122-00-3797	Delivery system 12/15/18	MGL
	7122-00-3837	Delivery System 6/18/10	MGL
	7122-00-3789	Fiber 12/15/18	MGL
	7122-00-8508	Delivery System w/o fiber 12/15/18	MGL
	7121-00-7220	GL snout	GL

	7121-00-7230	GL power meter head	GL
	7121-00-8000	beam shutter (large)	GL
	7121-00-7590	GLP delivery system no fiber	GL
MCH-18288	7121-00-7820	GLP handpiece shell	GL
	8050-01-1525	fiber lens cap lens	GL
	7121-00-6950	Key & Emergency stop switch	
MCH-18289	7122-00-3369	HP Shell	MGL/Y
	1301-00-7146	Plunger	
	1201-00-0020		
	7111-00-2680	HP Switch Board	MGL/Y
	1301-08-8046	Skin/Cover: Yag Left	MGL/Y

	1301-08-8047	Skin/Cover:Yag Right	MGL/Y
	7122-00-3422	Skin/Cover:front cover	
	1301-00-7047	Skin/Cover:Left or Right	GLP
	1301-00-7046	Skin/Cover:Front	GLP
	1301-00-7048	Skin/Cover:Top	GLP
	1510-00-7224	Capactor	MGL/Y
	7122-00-3361	Rod Alignment Tool	MGL/Y