


factory tested for leaks and function.

5. Each MVC utilizes an AB MicroLogix 1100 PLC. The PLC program sets the pulse duration time at one-half second, and allows the operator to select pulse frequency by way of a 3 position front mounted NEMA 4X selector switch. The



2 Valve/4 Output
Enclosure





Forming Plate

Photo and schematic of the Forming Plate.




Forming
Plate



Forming
Plate
Drawing
(PDF)

Typical Drawings


Examples of plate layouts for different tanks.




Technical




Technical



Drawings
(PDF)



Drawing
(PDF)



©Pulsed Hydraulics Inc. All rights reserved.

